



Actinic BL TL(-K)/TL-D(-K)

Actinic BL TL-D 18W/10 1SL/25

Tubular low-pressure mercury vapour fluorescent lamps

Product data

General Information	
Cap base	G13 [Medium Bi-Pin Fluorescent]
Main application	Insect traps
Life to 50% failures (nom.)	13000 h
Useful life (nom.)	9000 h
Light Technical	
Colour Code	10
Colour Designation	Actinic
Chromaticity coordinate X (nom.)	222
Chromaticity coordinate Y (nom.)	210
Depreciation at 500 Hours	8 %
Depreciation at 500 Hours	12 %
Depreciation at 500 Hours	16 %
Operating and Electrical	
Power (Rated) (Nom)	18 W
Lamp current (nom.)	0.36 A
Voltage (Nom)	59 V

Approval and Application	
Mercury (Hg) content (nom.)	5.0 mg
UV	
UV-B/UV-A (IEC)	0.2 %
UV-A radiation 100 hours (IEC)	5.0 W
Product Data	
Full product code	871150026325440
Order product name	Actinic BL TL-D 18W/10 1SL/25
EAN/UPC – product	8711500263254
Order code	26325440
Numerator – quantity per pack	1
Numerator – packs per outer box	25
Material no. (12NC)	928048001003
Net weight (piece)	71.000 g

Warnings and Safety



Actinic BL TL(-K)/TL-D(-K)

Dimensional drawing

Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL-D 18W/10 1SL/25	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm

TL-D 18W/10

Photometric data



Lightcolour /10

Lightcolour /10

