



# Jaundice TL/TL-D

## TL-D 18W/52

By emitting light almost entirely within the 400 to 500 nm bandwidth these Medical Therapy Jaundice TL/TL-D /52 lamps have no radiation from the short wave UVB waveband. They are therefore ideal for treating new born babies suffering from hyperbilirubinemia (neonatal jaundice) and Crigler-Najjar Syndrome (CNS). Moreover, the bandwidth of these lamps peak at the most effective treatment wavelength of 450 nm. This highly efficacious phototherapy treatment has eliminated the need for blood transfusions in almost all jaundiced infants.

### Product data

General Information	
Cap base	G13 [ Medium Bi-Pin Fluorescent]
Main application	Phototherapy Systems
Life to 50% failures (nom.)	13000 h
Useful life (nom.)	2000 h

Light Technical	
Colour code	52
Luminous flux (nom.)	395 lm
Chromaticity coordinate X (nom.)	157
Chromaticity coordinate Y (nom.)	75

Operating and Electrical	
Power (Rated) (Nom)	18 W
Lamp current (nom.)	0.36 A
Voltage (Nom)	59 V

Controls and Dimming	
Dimmable	Yes

Approval and Application	
Mercury (Hg) content (nom.)	13.0 mg


  

Product Data	
Full product code	872790083485700
Order product name	TL-D 18W/52
EAN/UPC – product	8727900834857
Order code	83485700
Numerator – quantity per pack	1
Numerator – packs per outer box	25
Material no. (12NC)	928048005211
Net weight (piece)	71.000 g

### Warnings and Safety

# Jaundice TL/TL-D

## Dimensional drawing



Product

TL-D 18W/52

TL-D 18W/52

