



Actinic BL TL-D(K) Secura

Actinic BL TL-D TL-D 18W/10 Secura 1SL/25

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL-D(K) Secura lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. In addition, they have a special "Secura" sleeve that keeps all glass and components together in the case of accidental breakage. This eliminates the risk of glass splinters showering down on food preparation areas, for example. And that is why it meets the strict HACCP requirements. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice.

Product data


General Information		Voltage (Nom)	
Cap base	G13 [Medium Bi-Pin Fluorescent]		59 V
Main application	Reprography (R)	Approval and Application	
Life to 50% failures (nom.)	13000 h	Mercury (Hg) content (nom.)	5.0 mg
Useful life (nom.)	9000 h	UV	
Light Technical		UV-B/UV-A (IEC)	0.2 %
Colour code	10	UV-A radiation 100 hours (IEC)	4.5 W
Colour designation	Actinic	Product Data	
Chromaticity coordinate X (nom.)	220	Full product code	872790085383400
Chromaticity coordinate Y (nom.)	200	Order product name	Actinic BL TL-D TL-D 18W/10 Secura 1SL/25
Depreciation at 500 Hours	20 %	EAN/UPC – product	8727900853834
Depreciation at 500 Hours	30 %	Order code	85383400
Operating and Electrical		Numerator – quantity per pack	1
Power (Rated) (Nom)	18 W	Numerator – packs per outer box	25
Lamp current (nom.)	0.36 A	Material no. (12NC)	928048201003

Actinic BL TL-D(K) Secura

Net weight (piece) 127.500 g

Warnings and Safety



Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL-D TL-D 18W/10 Secura 1SL/25	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm

TL-D 18W/10 SECU

Photometric data



XDPB_XUBTLD_10-Spectral power distribution B/W

