



# Actinic BL TL-D(K) Secura

## Actinic BL TL-D 18W/10 Secura 1SL/25

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL-D(K) Secura lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. In addition, they have a special "Secura" sleeve that keeps all glass and components together in the case of accidental breakage. This eliminates the risk of glass splinters showering down on food preparation areas, for example. And that is why it meets the strict HACCP requirements. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


| General Information             |                                 | UV Depreciation at 5,000 h |               |
|---------------------------------|---------------------------------|----------------------------|---------------|
| Cap base                        | G13 [Medium Bi-Pin Fluorescent] |                            | 30 %          |
| Life to 50% failures (nom.)     | 13,000 h                        | Operating and Electrical   |               |
| Useful life (nom.)              | 9,000 h                         | Power Consumption          | 18 W          |
| Light Technical                 |                                 | Lamp current (nom.)        | 0.36 A        |
| Colour Code                     | 10                              | Voltage (nom.)             | 59 V          |
| Colour designation              | Actinic                         | Voltage (nom.)             | 59 V          |
| Chromaticity Coordinate X (Nom) | 220                             | Mechanical and Housing     |               |
| Chromaticity Coordinate Y (Nom) | 200                             | Bulb shape                 | T26 [T 26 mm] |
| UV depreciation at 2,000 h      | 20 %                            |                            |               |

Actinic BL TL-D(K) Secura

|                                |                                      |
|--------------------------------|--------------------------------------|
| Approval and Application       |                                      |
| Mercury (Hg) content (nom.)    | 5.0 mg                               |
| UV                             |                                      |
| UV-A radiation 100 hours (IEC) | 4.5 W                                |
| Product Data                   |                                      |
| Order product name             | Actinic BL TL-D 18W/10 Secura 1SL/25 |
| Full product name              | Actinic BL TL-D 18W/10 Secura 1SL/25 |
| Full EOC                       | 872790085383400                      |


|                                   |               |
|-----------------------------------|---------------|
| Order code                        | 85383400      |
| Material no. (12 NC)              | 928048201003  |
| Local order code                  | 1810SEC       |
| SAP numerator – quantity per pack | 1             |
| EAN/UPC – Product/Case            | 8727900853834 |
| Numerator – packs per outer box   | 25            |
| EAN/UPC – Case                    | 8727900853841 |

Dimensional drawing



| Product                              | D (max) | A (max)  | B (max)  | B (min)  | C (max) |
|--------------------------------------|---------|----------|----------|----------|---------|
| Actinic BL TL-D 18W/10 Secura 1SL/25 | 28 mm   | 589.8 mm | 596.9 mm | 594.5 mm | 604 mm  |

Photometric data



Spectral Power Distribution Colour – Actinic BL TL-D 18W/10 Secura 1SL/25

