



MASTER TL-D Food

MASTER TL-D Food 36W/79 SLV/25

The TL-D Food lamp makes the appearance of meat and bakery products more fresh and tasty. It can be applied for food illumination in butcher shops, bakeries, supermarkets etc.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Controls and Dimming	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Dimmable	Yes
Life to 50% Failures (Nom)	15.000 hour(s)		
Light Technical		Mechanical and Housing	
Color Code	79	Bulb Shape	T8
Luminous Flux	1,750 lm		
Color Designation	Food	Approval and Application	
Correlated Color Temperature (Nom)	3800 K	Mercury (Hg) Content (Nom)	5.0 mg
Luminous Efficacy (rated) (Nom)	49 lm/W	Energy Consumption kWh/1000 h	43 kWh
Color rendering index (CRI)	74		
Operating and Electrical		Product Data	
Power Consumption	36.0 W	Order product name	MASTER TL-D Food 36W/79 SLV/25
Lamp Current (Nom)	0.440 A	Full product name	MASTER TL-D Food 36W/79 SLV/25
Voltage (Nom)	103 V	Full product code	871150070622540
Voltage (Nom)	103 V	Order code	928048502043
		Material Nr. (12NC)	928048502043
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8711500706225
		Numerator - Packs per outer box	25

MASTER TL-D Food

EAN/UPC - Case


8711500613127

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D Food 36W/79 SLV/25	28 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm

Photometric data




Spectral Power Distribution Colour - MASTER TL-D Food 36W/79 SLV/25

Lifetime




Life Expectancy Diagram - MASTER TL-D Food 36W/79 SLV/25



Life Expectancy Diagram - MASTER TL-D Food 36W/79 SLV/25

MASTER TL-D Food

Lifetime



Lumen Maintenance Diagram - MASTER TL-D Food 36W/79 SLV/25

