



TL-D Standard Colours

TL-D 58W/33-640 1SL/25

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Product data

General Information		Controls and Dimming	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Dimmable	Yes
Life to 50% Failures (Nom)	13,000 hour(s)		
Light Technical		Mechanical and Housing	
Color Code	33-640	Bulb Shape	T8
Luminous Flux	4,600 lm		
Color Designation	Cool White (CW)	Approval and Application	
Correlated Color Temperature (Nom)	4100 K	Mercury (Hg) Content (Nom)	5.0 mg
Color rendering index (CRI)	63	Energy Consumption kWh/1000 h	68 kWh
Operating and Electrical		Product Data	
Power Consumption	58.5 W	Order product name	TL-D 58W/33-640 1SL/25
Lamp Current (Nom)	0.670 A	Full product name	TL-D 58W/33-640 1SL/25
Voltage (Nom)	111 V	Full product code	871150095049940
Voltage (Nom)	111 V	Order code	928049003312
		Material Nr. (12NC)	928049003312
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8711500950499
		Numerator - Packs per outer box	25

TL-D Standard Colours


EAN/UPC - Case	8711500950505
----------------	---------------

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 58W/33-640 1SL/25	28 mm	1,500.0 mm	1,507.1 mm	1,504.7 mm	1,514.2 mm

Photometric data




Spectral Power Distribution Colour - TL-D 58W/33-640 1SL/25

Lifetime




Life Expectancy Diagram - TL-D 58W/33-640 1SL/25



Life Expectancy Diagram - TL-D 58W/33-640 1SL/25

TL-D Standard Colours

Lifetime



Lumen Maintenance Diagram - TL-D 58W/33-640 1SL/25

