



TL-D Standard Colours

TL-D 58W/54 1SL/25

TL-D Standard Colors lamps (tube diameter of 26 mm) create atmospheres from warm white to cool daylight. Lamps with moderate efficacy and color rendering.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Life To 10% Failures (Nom)	10000 h
Life to 50% Failures (Nom)	13000 h

Light Technical	
Color Code	54-765
Luminous Flux (Nom)	4000 lm
Color Designation	Cool Daylight
Lumen Maintenance 10000 h (Nom)	75 %
Lumen Maintenance 2000 h (Nom)	90 %
Lumen Maintenance 5000 h (Nom)	80 %
Correlated Color Temperature (Nom)	6200 K
Color Rendering Index (Nom)	72

Operating and Electrical	
Power (Nom)	58.5 W
Lamp Current (Nom)	0.670 A
Voltage (Nom)	111 V

Controls and Dimming	
Dimmable	Yes


Approval and Application	
Energy Efficiency Label (EEL)	B
Mercury (Hg) Content (Nom)	8.0 mg
Energy Consumption kWh/1000 h	68 kWh

Product Data	
Full product code	872790091864900
Order product name	TL-D 58W/54 1SL/25
EAN/UPC - Product	8727900918649
Order code	928049005481
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	25
Material Nr. (12NC)	928049005481
Net Weight (Piece)	167.000 g
ILCOS Code	FD-58/62/2A-E-G13

Warnings and Safety

TL-D Standard Colours


Dimensional drawing




TL-D 58W/54-765

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D 58W/54 1SL/25	28 mm	1500.0 mm	1507.1 mm	1504.7 mm	1514.2 mm

Photometric data




LDPB_TL-DSTD_54-765-Spectral power distribution B/W




LDPO_TL-DSTD_54-765-Spectral power distribution Colour

Lifetime



LDLE_TL-DSTD_0001-Life expectancy diagram



TL-D Standard Colours

Lifetime



LDLM_TL-DSTD_0001-Lumen maintenance diagram

