



MSR Hot Restrike

MSR 4000 HR 1CT/1

High-efficiency hot restrike metal halide lamps designed for optimum light collection

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Product data

General Information	
Cap-Base	G38 [G38]
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	300 hour(s)
Light Technical	
Color Code	- [Not Specified]
Luminous Flux (Min)	331,200 lm
Luminous Flux	368,000 lm
Chromaticity Coordinate X (Nom)	304
Chromaticity Coordinate Y (Nom)	310
Correlated Color Temperature (Nom)	7270 K
Luminous Efficacy (rated) (Nom)	92 lm/W
Color rendering index (CRI)	88
Arc Length O (Nom)	20.0 mm
Operating and Electrical	
Power Consumption	4,000 W

Lamp Current (Nom)	25.8 A
Controls and Dimming	
Dimmable	Yes
Product Data	
Order product name	MSR 4000 HR 1CT/1
Full product name	MSR 4000 HR 1CT/1
Full product code	87279009267600
Order code	928050405114
Material Nr. (12NC)	928050405114
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900926767
Numerator - Packs per outer box	1
EAN/UPC - Case	8727900926774


MSR Hot Restrike

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSR 4000	77 mm	20.0	141 mm	143 mm	142	255 mm	67 mm	65	63 mm
HR 1CT/1		mm			mm			mm	

Photometric data



Spectral Power Distribution Colour – MSR 4000 HR 1CT/1

