



MSR Hot Restrike

MSR 4000 HR 1CT/1

Thanks to an optimized color temperature and a high color rendering index, the MSR Hot Restrike creates perfect 'daylight' in any condition. Also, the single ended lamp design enables hot re-ignition, which ensures daylight lighting and superb color rendition is always instantly available. They also incorporate the innovative P3 technology, developed by Philips, which allows use at higher temperatures and therefore extends lifetime and consistency of high-quality light output.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	G38
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	300 hour(s)
Light Technical	
Color Code	- [Not Specified]
Luminous Flux (Min)	331,200 lm
Luminous Flux	368,000 lm
Chromaticity Coordinate X (Nom)	304
Chromaticity Coordinate Y (Nom)	310
Correlated Color Temperature (Nom)	7270 K
Luminous Efficacy (rated) (Nom)	92 lm/W


Color rendering index (CRI)	88
Arc Length O (Nom)	20.0 mm
Operating and Electrical	
Power Consumption	4,000 W
Lamp Current (Nom)	25.8 A
Controls and Dimming	
Dimmable	Yes
Product Data	
Order product name	MSR 4000 HR 1CT/1
Full product name	MSR 4000 HR 1CT/1

MSR Hot Restrike

Full product code	872790092676700
Order code	245894
Material Nr. (12NC)	928050405114
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900926767


Numerator - Packs per outer box	1
EAN/UPC - Case	8727900926774

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSR	3-1/16	13/16	5-9/16	5-5/8	5-5/8	10-1/16	2-11/16	2-9/16	2-1/2
4000 HR	inch	inch	inch	inch	inch	inch	inch	inch	inch
1CT/1									

Photometric data



Spectral Power Distribution Colour - MSR 4000 HR 1CT/1

