



HPL-N

HPL-N 125W/542 E27 1CT/24

标准高压汞灯

安全提示

- For use with control gear designed for high-pressure mercury lamps
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据


一般信息	
底盖	E27 [E27]
操作位置	UNIVERSAL [任意或通用 (U)]
50% 故障条件下的使用寿命 (标称)	20,000 小时
灯技术	
颜色代码	542 [CCT of 4200K]
颜色名称	冷白色 (CW)
色度坐标 X (标称)	374
色度坐标 Y (标称)	373
相关色温 (标称)	4100 K
光效 (额定) (标称)	50 lm/W
显色指数 (CRI)	46
操作和电气	
功耗	125.0 W
电压 (标称)	125 V
电压 (标称)	125 V

控制和调光	
可调光	否
机械和外壳	
灯泡外观	镀膜玻璃
灯泡材料	软玻璃
灯泡外形	E75 [E 75 毫米]
审批和申请	
汞 (Hg) 含量 (标称)	19.0 mg
能耗 kWh/1000 h	137 kWh
产品数据	
订单产品名称	HPL-N 125W/542 E27 1CT/24
完整的产品名称	HPL-N 125W/542 E27 1CT/24
完整产品代码	692059027779500
订购代码	928052007391
材料编号 (12NC)	928052007391
计算器 - 每包数量	1
EAN/UPC - 产品/箱	6920590277795

HPL-N


计算器 - 每个外包装箱中的包数	24
EAN/UPC - 案例	6920590277801

二维绘图




Product	D (max)	C (max)
HPL-N 125W/542 E27 1CT/24	76 mm	173 mm

光度数据




Spectral Power Distribution Colour - HPL-N 125W/542 E27 1CT/24

寿命



Life Expectancy Diagram - HPL-N 125W/542 E27 1CT/24



Lumen Maintenance Diagram - HPL-N 125W/542 E27 1CT/24

