



# HPL-N

## HPL-N 400W/542 E40 HG 1SL/6

Standard High Pressure Mercury lamp

### Product data

General Information	
Cap base	E40 [ E40]
Burning Position	UNIVERSAL [ Any/Universal]
Life to 5% failures (nom.)	6000 h
Life to 20% failures (nom.)	12000 h
Life to 50% failures (nom.)	16000 h
LSF 2000 h Rated	99 %
LSF 4000 h Rated	97 %
LSF 6000 h Rated	92 %
LSF 8000 h Rated	83 %
LSF 12000 h Rated	65 %
LSF 16000 h Rated	45 %
LSF 20000 h Rated	28 %
Light Technical	
Colour Code	542 [ CCT of 4,200 K]
Lamp Luminous Flux (Nom)	22000 lm
Colour Designation	Cool White (CW)
Lumen maintenance 2,000 hours (min.)	78 %
Lumen maintenance 2,000 hours (nom.)	88 %
Lumen maintenance 5,000 hours (min.)	75 %
Lumen maintenance 5,000 hours (nom.)	85 %
Chromaticity coordinate X (nom.)	384
Chromaticity coordinate Y (nom.)	384
Colour Temperature, horizontal (Nom)	4200 K
Lamp Luminous Efficacy EM (Nom)	55 lm/W

Colour Rendering Index,horiz (Nom)	50
LLMF 2000 h Rated	88 %
LLMF 4000 h Rated	86 %
LLMF 6000 h Rated	84 %
LLMF 8000 h Rated	82 %
LLMF 12000 h Rated	78 %
LLMF 16000 h Rated	75 %
LLMF 20000 h Rated	72 %

### Operating and Electrical

Power (Rated) (Nom)	400.0 W
Lamp current (EM) (nom.)	3.25 A
Ignition supply voltage (max.)	170 V
Voltage (Max)	150 V
Voltage (Min)	130 V
Voltage (Nom)	140 V

### Controls and Dimming

Dimmable	no
----------	----

### Mechanical and Housing

Bulb finish	Coated glass
Bulb material	Hard Glass

### Approval and Application

Energy efficiency label (EEL)	B
-------------------------------	---

# HPL-N

Mercury (Hg) content (nom.)	72 mg
Energy Consumption kWh/1000 h	440 kWh
<b>Luminaire Design Requirements</b>	
Bulb temperature (max.)	350 °C
Cap base temperature (max.)	210 °C
<b>Product Data</b>	
Full product code	871150018045299
Order product name	HPL-N 400W/542 E40 HG 1SL/6

EAN/UPC – product	8711500180452
Order code	928053507496
Local Code	HPLN400WGES
Numerator – quantity per pack	1
Numerator – packs per outer box	6
Material no. (12NC)	928053507496
Net weight (piece)	0.255 kg
ILCOS Code	QE-400/40/3-H-E40

## Warnings and Safety


## Dimensional drawing

D

Product	D (max)	C (max)
HPL-N 400W/542 E40 HG 1SL/6	122 mm	290 mm



HPL N 400W E40 HG

## Photometric data



# HPL-N

## Lifetime



LDLM\_HPL\_0001-Lumen maintenance diagram

