



# MSR Hot Restrike

## MSR 125 HR 1CT/4

Thanks to an optimized color temperature and a high color rendering index, the MSR Hot Restrike creates perfect 'daylight' in any condition. Also, the single ended lamp design enables hot re-ignition, which ensures daylight lighting and superb color rendition is always instantly available. They also incorporate the innovative P3 technology, developed by Philips, which allows use at higher temperatures and therefore extends lifetime and consistency of high-quality light output.

### Product data

General Information	
Base	GZX9.5 [ GZX9.5]
Operating Position	Universal [ Universal]
Main Application	Studio/Theatre
Life to 50% Failures (Nom)	200 h
System Description	Hot Restrike
Light Technical	
Color Code	- [ Not Specified]
Initial lumen (Min)	8000 lm
Initial lumen (Nom)	9400 lm
Chromaticity Coordinate X (Nom)	332
Chromaticity Coordinate Y (Nom)	326
Correlated Color Temperature (Nom)	6000 K
Luminous Efficacy (rated) (Nom)	75 lm/W
Color Rendering Index (Nom)	92
Operating and Electrical	
Power (Rated) (Nom)	125 W
Lamp Current (Nom)	1.9 A
Ignition Supply Voltage (Min)	207 V


Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Cap-Base Information	na [ -]
Luminaire Design Requirements	
Bulb Temperature (Max)	700 °C
Pinch Temperature (Max)	350 °C
Product Data	
Order product name	MSR 125 HR 1CT/4
EAN/UPC - Product	8718696414927
Order code	261354
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	928060205115
Net Weight (Piece)	18.000 g

# MSR Hot Restrike

## Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury. Manage in Accord with Disposal Laws. See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050



## Dimensional drawing



MSR 125 HR

Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSR 125	17 mm	4.0	38 mm	40 mm	39	77 mm	24 mm	23.5	23 mm
HR 1CT/4		mm			mm			mm	

## Photometric data



XDPO\_XDMSR\_HR\_--Spectral power distribution Colour

