



PHILIPS

Lighting



MASTER MHN-LA

MASTER MHN-LA 1000W/956 230V XWH

Compact quartz metal halide lamps with double-pin

Product data

General Information	
Cap base	X528 [X528]
Operating position	P5 [Parallel +/-5D or Horizontal(HOR)]
Life to 5% failures (nom.)	6000 h
Life to 10% failures (nom.)	8000 h
Life to 20% failures (nom.)	10000 h
Life to 50% failures (nom.)	15000 h
Light Technical	
Colour code	956 [CCT of 5,600 K]
Luminous flux (rated) (min.)	82000 lm
Luminous flux (rated) (nom.)	87000 lm
Colour designation	Daylight
Lumen maintenance 1,000 hours (nom.)	90 %
Lumen maintenance 2,000 hours (nom.)	80 %
Chromaticity coordinate X (nom.)	337
Chromaticity coordinate Y (nom.)	331
Correlated Colour Temperature (Nom)	5600 K
Luminous efficacy (rated) (nom.)	86.0 lm/W
Color rendering index (nom.)	80
Operating and Electrical	
Lamp supply voltage	230 V [230]
Power (Rated) (Nom)	1040.0 W
Lamp current run-up (max.)	15 A
Lamp current (EM) (nom.)	9.3 A

Ignition supply voltage (min.)	198 V
Voltage (Max)	140 V
Voltage (Min)	110 V
Voltage (Nom)	125 V
Controls and Dimming	
Dimmable	no
Mechanical and Housing	
Bulb finish	Clear
Cap base information	Cable (C)
Approval and Application	
Energy efficiency label (EEL)	A
Mercury (Hg) content (nom.)	95 mg
Energy Consumption kWh/1000 h	1144 kWh
UV	
Specific eff. radiant power	270 mW/klm
Luminaire Design Requirements	
Bulb temperature (max.)	920 °C
Pinch temperature (max.)	350 °C
Product Data	
Full product code	871150020077800

MASTER MHN-LA

Order product name	MASTER MHN-LA 1000W/956 230V XWH
EAN/UPC – product	8718291548218
Order code	20077800
Local Code	1000MHNLA956
Numerator – quantity per pack	1
Numerator – packs per outer box	1

Material no. (12NC)	928072205130
Net weight (piece)	132.000 g
ILCOS Code	MN-1000-E-K-/H

Warnings and Safety


Dimensional drawing



Product	D (max)	O	X	A
MASTER MHN-LA 1000W/956 230V XWH	40 mm	40.5 mm	35 mm	286 mm


MHN-LA 1000W/956 230V XWH

Photometric data



MASTER MHN-LA

Lifetime



LDLM_MHN-LA_0001-Lumen maintenance diagram

