


MASTER MHN-LA 複金屬燈

MASTER MHN-LA 2000W/956 400V XWH

雙封式袖珍型石英複金屬燈

安全提示

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般資訊	
燈座基底	X528
操作位置	P5 [平行 +/-5D 或水平 (HOR)]
壽命 (故障率 50%) (標稱)	13,000 h

照明技術	
色碼	956 [CCT of 5600K]
色彩名稱	日光
色度坐標 X (標稱)	330
色度坐標 Y (Nom)	339
相關色彩溫度 (規範)	5600 K
光效 (額定) (標準)	93 lm/W
演色性指數 (CRI)	82
電弧長 O (標稱)	108 mm

運轉與電力	
耗電量	2,040.0 W
電壓 (標稱)	225 V
電壓 (標稱)	225 V

控制與調光	
可調光	否

機械與外罩	
燈泡表層	透明
燈泡形狀	TD40

認證與應用	
汞 (Hg) 含量 (標稱)	140 mg
能源消耗 kWh/1000 h	2244 kWh


產品資料	
下訂產品名稱	MASTER MHN-LA 2000W/956 400V XWH
完整產品名稱	MASTER MHN-LA 2000W/956 400V XWH

MASTER MHN-LA 複金屬燈

完整產品代碼	871150020073000
訂單代碼	928072505130
材質 Nr. (12NC)	928072505130
分子 - 每個包裝的數量	1
EAN/UPC - 產品/案例	8718291548225


分子 - 每一外盒包裝	1
EAN/UPC - 箱	8711500200730

二维绘图




Product	D (max)	O	X	A
MASTER MHN-LA 2000W/956 400V XWH	40 mm	108 mm	58 mm	353 mm

光度数据



Spectral Power Distribution Colour - MASTER MHN-LA 2000W/956 400V XWH

壽命



Life Expectancy Diagram - MASTER MHN-LA 2000W/956 400V XWH

Lumen Maintenance Diagram - MASTER MHN-LA 2000W/956 400V XWH

© 2023 Signify Holding 保留一切權利。 Signify 不對本協議所含括資訊之準確性及完整性提供任何聲明或保證，對以此訊息為依據採取的任何行動亦概不負責。 除非 Signify 同意，本文件提及之資訊並非任何商業合約，亦不構成任何報價或合約任一部分。 Philips 與 Philips Shield Emblem 均屬 Koninklijke Philips N.V 註冊商標。

www.lighting.philips.com
2023, 四月 16 - 要更改的数据主题