



# HPI-T High Wattage

## HPI-T 2000W/646 E40 220V CRP/4

Quartz metal halide lamps with clear outer bulb

### Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- For use with control gear designed for high-pressure mercury lamps
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

| General Information                |  |
|------------------------------------|--|
| Cap-Base                           | E40 [E40]                                |
| Operating Position                 | P75 [Parallel +/-75D or Horizontal(HOR)] |
| Life to 50% Failures (Nom)         | 12,000 hour(s)                           |
| Light Technical                    |  |
| Color Code                         | 646 [CCT of 4600K]                       |
| Color Designation                  | Cool White (CW)                          |
| Chromaticity Coordinate X (Nom)    | 375                                      |
| Chromaticity Coordinate Y (Nom)    | 385                                      |
| Correlated Color Temperature (Nom) | 4200 K                                   |
| Luminous Efficacy (rated) (Nom)    | 95 lm/W                                  |
| Color rendering index (CRI)        | 63                                       |
| Arc Length O (Nom)                 | 89 mm                                    |
| Operating and Electrical           |  |
| Power Consumption                  | 1,980 W                                  |
| Voltage (Nom)                      | 130 V                                    |


| Voltage (Nom)                 | 130 V                          |
|-------------------------------|--------------------------------|
| Controls and Dimming          |                                |
| Dimmable                      | No                             |
| Mechanical and Housing        |                                |
| Bulb Finish                   | Clear                          |
| Bulb Shape                    | T100 [T 100mm]                 |
| Approval and Application      |                                |
| Mercury (Hg) Content (Nom)    | 155 mg                         |
| Energy Consumption kWh/1000 h | 2178 kWh                       |
| Product Data                  |                                |
| Order product name            | HPI-T 2000W/646 E40 220V CRP/4 |
| Full product name             | HPI-T 2000W/646 E40 220V CRP/4 |
| Full product code             | 871150018376745                |
| Order code                    | 928073609231                   |

HPI-T High Wattage

|                                 |               |
|---------------------------------|---------------|
| Material Nr. (12NC)             | 928073609231  |
| Numerator - Quantity Per Pack   | 1             |
| EAN/UPC - Product/Case          | 8711500183767 |
| Numerator - Packs per outer box | 4             |


|                |               |
|----------------|---------------|
| EAN/UPC - Case | 8711500183774 |
|----------------|---------------|

Dimensional drawing




| Product                        | D (max)  | O     | L      | C (max) |
|--------------------------------|----------|-------|--------|---------|
| HPI-T 2000W/646 E40 220V CRP/4 | 101.5 mm | 89 mm | 290 mm | 430 mm  |

Photometric data




Spectral Power Distribution Colour - HPI-T 2000W/646 E40 220V CRP/4

Lifetime



Life Expectancy Diagram - HPI-T 2000W/646 E40 220V CRP/4



Lumen Maintenance Diagram - HPI-T 2000W/646 E40 220V CRP/4

## HPI-T High Wattage

