PHILIPS Lighting



MASTER HPI Plus

MASTER HPI Plus 400W/645 BU E40 1SL/6

Quartz metal halide lamps with opalized outer bulb

Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- For use with control gear designed for high-pressure mercury or sodium lamps
- For use with control gear designed for high-pressure mercury or sodium lamps
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Color rendering index (CRI)	65
Cap-Base	E40 [E40]		
Operating Position	H15 [Hanging +/-15D or Base Up (BU)]	Operating and Electrical	
Life to 50% Failures (Nom)	20,000 hour(s)	Power Consumption	405 W
		Voltage (Nom)	125 V
Light Technical		Voltage (Nom)	125 V
Color Code	645 [CCT of 4500K]		
Color Designation	Cool White (CW)	Controls and Dimming	
Chromaticity Coordinate X (Nom)	367	Dimmable	No
Chromaticity Coordinate Y (Nom)	374		
Correlated Color Temperature (Nom)	4500 K	Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	80 lm/W	Bulb Finish	Coated glass

MASTER HPI Plus

Bulb Shape	BD120 [BD 120mm]	
Approval and Application		
Mercury (Hg) Content (Nom)	67 mg	
Energy Consumption kWh/1000 h	446 kWh	
Product Data		
Order product name	MASTER HPI Plus 400W/645 BU E40 1SL/6	
Full product name	MASTER HPI Plus 400W/645 BU E40 1SL/6	


Full product code	871150018252410
Order code	928074309891
Material Nr. (12NC)	928074309891
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500182524
Numerator - Packs per outer box	6
EAN/UPC - Case	8711500182531


Dimensional drawing




Product	D (max)	C (max)
MASTER HPI Plus 400W/645 BU E40 1SL/6	122 mm	290 mm

Photometric data






Light Distribution Diagram - MASTER HPI Plus 400W/645 BU E40 1SL/6



Spectral Power Distribution Colour - MASTER HPI Plus 400W/645 BU E40 1SL/6

MASTER HPI Plus

Lifetime



Life Expectancy Diagram - MASTER HPI Plus 400W/645 BU E40 1SL/6

Lumen Maintenance Diagram - MASTER HPI Plus 400W/645 BU E40 1SL/6



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2023, April 16 - data subject to change