



# MASTER HPI Plus

## MASTER HPI Plus 400W/667 BU E40 1SL/6

Quartz metal halide lamps with opalized outer bulb

### Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- For use with control gear designed for high-pressure mercury or sodium lamps
- For use with control gear designed for high-pressure mercury or sodium lamps
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


General Information		Color rendering index (CRI)	
Cap-Base	E40 [E40]		60
Operating Position	H15 [Hanging +/-15D or Base Up (BU)]	Operating and Electrical	
Life to 50% Failures (Nom)	20,000 hour(s)	Power Consumption	405 W
Light Technical		Voltage (Nom)	125 V
Color Code	667 [CCT of 6700K]	Voltage (Nom)	125 V
Color Designation	Daylight	Controls and Dimming	
Chromaticity Coordinate X (Nom)	310	Dimmable	No
Chromaticity Coordinate Y (Nom)	341	Mechanical and Housing	
Correlated Color Temperature (Nom)	6700 K	Bulb Finish	Coated glass
Luminous Efficacy (rated) (Nom)	80 lm/W		

# MASTER HPI Plus

Bulb Shape	BD120 [BD 120mm]
<b>Approval and Application</b>	
Mercury (Hg) Content (Nom)	67 mg
Energy Consumption kWh/1000 h	434 kWh
<b>Product Data</b>	
Order product name	MASTER HPI Plus 400W/667 BU E40 1SL/6
Full product name	MASTER HPI Plus 400W/667 BU E40 1SL/6



Full product code	871150020737110
Order code	928074409894
Material Nr. (12NC)	928074409894
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500207371
Numerator - Packs per outer box	6
EAN/UPC - Case	8711500207388

## Dimensional drawing



Product	D (max)	C (max)
MASTER HPI Plus 400W/667 BU E40 1SL/6	122 mm	290 mm

## Photometric data





Light Distribution Diagram - MASTER HPI Plus 400W/667 BU E40 1SL/6

Spectral Power Distribution Colour - MASTER HPI Plus 400W/667 BU E40 1SL/6

# MASTER HPI Plus

## Lifetime



Life Expectancy Diagram - MASTER HPI Plus 400W/667 BU E40 1SL/6

Lumen Maintenance Diagram - MASTER HPI Plus 400W/667 BU E40 1SL/6

