



MASTER HPI Plus

MASTER HPI Plus 250W/667 BU E40 1SL/12

Quartz metal halide lamps with opalized outer bulb

Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- For use with control gear designed for high-pressure mercury or sodium lamps
- For use with control gear designed for high-pressure mercury or sodium lamps
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	E40 [E40]
Operating Position	H15 [Hanging +/-15D or Base Up (BU)]
Life to 50% Failures (Nom)	20,000 hour(s)
Light Technical	
Color Code	667 [CCT of 6700K]
Color Designation	Daylight
Chromaticity Coordinate X (Nom)	308
Chromaticity Coordinate Y (Nom)	318
Correlated Color Temperature (Nom)	6700 K
Luminous Efficacy (rated) (Nom)	72 lm/W


Color rendering index (CRI)	69
Operating and Electrical	
Power Consumption	253.0 W
Voltage (Nom)	128 V
Voltage (Nom)	128 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Coated glass

MASTER HPI Plus

Bulb Shape	BD90 [BD 90mm]
Approval and Application	
Mercury (Hg) Content (Nom)	47 mg
Energy Consumption kWh/1000 h	278 kWh
Product Data	
Order product name	MASTER HPI Plus 250W/667 BU E40 1SL/12
Full product name	MASTER HPI Plus 250W/667 BU E40 1SL/12



Full product code	871150020739515
Order code	928076809894
Material Nr. (12NC)	928076809894
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500207395
Numerator - Packs per outer box	12
EAN/UPC - Case	8711500207401

Dimensional drawing



Product	D (max)	C (max)
MASTER HPI Plus 250W/667 BU E40 1SL/12	91 mm	226 mm

Photometric data




Light Distribution Diagram - MASTER HPI Plus 250W/667 BU E40 1SL/12


Spectral Power Distribution Colour - MASTER HPI Plus 250W/667 BU E40 1SL/12

MASTER HPI Plus

Lifetime



Life Expectancy Diagram - MASTER HPI Plus 250W/667 BU E40 1SL/12



Lumen Maintenance Diagram - MASTER HPI Plus 250W/667 BU E40 1SL/12

