



# MSR

## MSR 700 1CT/8

The high color rendering index of the single ended MSR series ensures that everyone in the audience can enjoy the true colors of the scenery, the stage props, the players and their costumes – in fact everything that is on stage can be made bright and vivid in daylight quality light. Also, thanks to the single ended lamp concept, the luminaire has optimal light collection and direction possibilities to help ensure brightness on stage exactly where and when it is needed. In addition, the MSR can be used in any burning position for easy set-up and convenience.

### Product data

General Information	
Cap base	G22 [ G22]
Operating position	UNIVERSAL [ Any or Universal (U)]
Main application	Studio/Disco
Life to 50% failures (nom.)	1000 h
System description	na [ -]
Light Technical	
Colour code	- [ Not Specified]
Luminous flux (min.)	48000 lm
Luminous flux (nom.)	55000 lm
Chromaticity coordinate X (nom.)	325
Chromaticity coordinate Y (nom.)	320
Correlated colour temperature (nom.)	5900 K
Luminous efficacy (rated) (nom.)	80 lm/W
Color rendering index (nom.)	75
Operating and Electrical	
Power (Rated) (Nom)	700 W
Lamp current (nom.)	12 A


Ignition supply voltage (min.)	207 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Cap base information	na [ -]
Luminaire Design Requirements	
Bulb temperature (max.)	700 °C
Pinch temperature (max.)	350 °C
Product Data	
Full product code	872790091575400
Order product name	MSR 700 1CT/8
EAN/UPC – product	8727900915754
Order code	91575400
Numerator – quantity per pack	1
Numerator – packs per outer box	8
Material no. (12NC)	928078005114

# MSR

Net weight (piece) 0.120 kg

## Warnings and Safety

## Dimensional drawing





MSR 700

## Product

MSR 700 ICT/8

## Photometric data



XDPO\_XDMSR\_700\_--Spectral power distribution Colour

