



# MSR

## MSR 700 1CT/8

The high color rendering index of the single ended MSR series ensures that everyone in the audience can enjoy the true colors of the scenery, the stage props, the players and their costumes – in fact everything that is on stage can be made bright and vivid in daylight quality light. Also, thanks to the single ended lamp concept, the luminaire has optimal light collection and direction possibilities to help ensure brightness on stage exactly where and when it is needed. In addition, the MSR can be used in any burning position for easy set-up and convenience.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

### Product data


General Information		Color rendering index (CRI)	
Cap-Base	G22		75
Operating Position	UNIVERSAL [Any or Universal (U)]	Arc Length O (Nom)	8.0 mm
Life to 50% Failures (Nom)	1,000 hour(s)	<b>Operating and Electrical</b>	
<b>Light Technical</b>		Power Consumption	700 W
Color Code	- [Not Specified]	Lamp Current (Nom)	12 A
Luminous Flux	55,000 lm	<b>Controls and Dimming</b>	
Chromaticity Coordinate X (Nom)	325	Dimmable	No
Chromaticity Coordinate Y (Nom)	320	<b>Product Data</b>	
Correlated Color Temperature (Nom)	5900 K	Order product name	MSR 700 1CT/8
Luminous Efficacy (rated) (Nom)	80 lm/W		

# MSR

Full product name	MSR 700 1CT/8
Full product code	872790091575400
Order code	245423
Material Nr. (12NC)	928078005114
Numerator - Quantity Per Pack	1


EAN/UPC - Product/Case	8727900915754
Numerator - Packs per outer box	8
EAN/UPC - Case	8727900915761

## Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F
MSR 700	1-3/16 inch	5/16	2-15/16 inch	3 inch	3 inch	6 inch	1-11/16
1CT/8		inch					inch

## Photometric data



Spectral Power Distribution Colour - MSR 700 1CT/8

