



MSR

MSR 700 1CT/8

The high color rendering index of the single ended MSR series ensures that everyone in the audience can enjoy the true colors of the scenery, the stage props, the players and their costumes – in fact everything that is on stage can be made bright and vivid in daylight quality light. Also, thanks to the single ended lamp concept, the luminaire has optimal light collection and direction possibilities to help ensure brightness on stage exactly where and when it is needed. In addition, the MSR can be used in any burning position for easy set-up and convenience.

Product data


| General Information | |
|------------------------------------|------------------------|
| Base | G22 [G22] |
| Operating Position | Universal [Universal] |
| Main Application | Studio/Disco |
| Life to 50% Failures (Nom) | 1000 h |
| System Description | na [-] |
| Light Technical | |
| Color Code | - [Not Specified] |
| Initial lumen (Min) | 48000 lm |
| Initial lumen (Nom) | 55000 lm |
| Chromaticity Coordinate X (Nom) | 325 |
| Chromaticity Coordinate Y (Nom) | 320 |
| Correlated Color Temperature (Nom) | 5900 K |
| Luminous Efficacy (rated) (Nom) | 80 lm/W |
| Color Rendering Index (Nom) | 75 |
| Operating and Electrical | |
| Power (Rated) (Nom) | 700 W |
| Lamp Current (Nom) | 12 A |

| Ignition Supply Voltage (Min) | 207 V |
|---------------------------------|---------------|
| Controls and Dimming | |
| Dimmable | No |
| Mechanical and Housing | |
| Cap-Base Information | na [-] |
| Luminaire Design Requirements | |
| Bulb Temperature (Max) | 700 °C |
| Pinch Temperature (Max) | 350 °C |
| Product Data | |
| Order product name | MSR 700 1CT/8 |
| EAN/UPC - Product | 8727900915754 |
| Order code | 245423 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 8 |
| Material Nr. (12NC) | 928078005114 |
| Net Weight (Piece) | 0.120 kg |

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050



Dimensional drawing



| Product | D (max) | O | L (min) | L (max) | L | C (max) | F |
|---------------|---------|--------|---------|---------|-------|---------|-------|
| MSR 700 ICT/8 | 30 mm | 8.0 mm | 74 mm | 76 mm | 75 mm | 152 mm | 42 mm |

MSR 700

Photometric data



MSR 700

MSR 700

