



MSR

MSR 1200 1CT/3

The high color rendering index of the single ended MSR series ensures that everyone in the audience can enjoy the true colors of the scenery, the stage props, the players and their costumes – in fact everything that is on stage can be made bright and vivid in daylight quality light. Also, thanks to the single ended lamp concept, the luminaire has optimal light collection and direction possibilities to help ensure brightness on stage exactly where and when it is needed. In addition, the MSR can be used in any burning position for easy set-up and convenience.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050


Product data

General Information		Color rendering index (CRI)		80
Cap-Base	G22	Arc Length O (Nom)		10.0 mm
Operating Position	UNIVERSAL [Any or Universal (U)]			
Life to 50% Failures (Nom)	800 hour(s)			
Light Technical				
Color Code	- [Not Specified]			
Luminous Flux	103,000 lm			
Chromaticity Coordinate X (Nom)	325			
Chromaticity Coordinate Y (Nom)	327			
Correlated Color Temperature (Nom)	5900 K			
Luminous Efficacy (rated) (Nom)	88 lm/W			
Operating and Electrical				
Power Consumption		1,200 W		
Lamp Current (Nom)		13.8 A		
Controls and Dimming				
Dimmable		No		
Product Data				
Order product name		MSR 1200 1CT/3		

Full product name	MSR 1200 1CT/3
Full product code	872790091121300
Order code	245514
Material Nr. (12NC)	928078105114
Numerator - Quantity Per Pack	1


EAN/UPC - Product/Case	8727900911213
Numerator - Packs per outer box	3
EAN/UPC - Case	8727900911220

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F
MSR 1200	1-5/8	7/16	3-5/16	3-7/16	3-3/8	6-15/16	2-1/8
1CT/3	inch	inch	inch	inch	inch	inch	inch

Photometric data



Spectral Power Distribution Colour - MSR 1200 1CT/3

