



# MasterColor CDM-T6

## CDM150/T6/830 12PK

MasterColor CDM lamp gives a unique combination of unbeatable light quality and consistent performance over lifetime while keeping running costs low. The Philips MasterColor Tubular Single-Ended T6 lamp is a compact, energy efficient, ceramic metal halide lamp that provides crisp, sparkling light.

### Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

### Product data


General Information		Luminous Efficacy (rated) (Nom)	
Cap-Base	G12	88 lm/W	
Operating Position	UNIVERSAL [Any or Universal (U)]	Color rendering index (CRI)	
Life to 50% Failures (Nom)	12,000 hour(s)	88	
Light Technical		Arc Length O (Nom)	
Color Code	830 [CCT of 3000K]	9 mm	
Color Designation	Warm White (WW)	Operating and Electrical	
Chromaticity Coordinate X (Nom)	0.436	Power Consumption	
Chromaticity Coordinate Y (Nom)	0.396	150.1 W	
Correlated Color Temperature (Nom)	3000 K	Voltage (Nom)	
		96 V	
		Voltage (Nom)	
		96 V	

# MasterColor CDM-T T6

Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T19
Approval and Application	
Mercury (Hg) Content (Nom)	14.3 mg
Energy Consumption kWh/1000 h	162 kWh


Product Data	
Order product name	CDM150/T6/830 12PK
Full product name	CDM150/T6/830 12PK
Order code	232728
Material Nr. (12NC)	928083705115
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677232726
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677232721

## Dimensional drawing




Product	D (max)	D	O	L (min)	L (max)	L	C (max)
CDM150/ T6/830 12PK	13/16 inch	0.75 inch	3/8 inch	2-3/16 inch	2-1/4 inch	2-1/4 inch	4-3/8 inch

## Photometric data




Light Distribution Diagram - CDM150/T6/830 12PK




Spectral Power Distribution Colour - CDM150/T6/830 12PK

MasterColor CDM-T T6

Lifetime



Life Expectancy Diagram - CDM150/T6/830 12PK



Lumen Maintenance Diagram - CDM150/T6/830 12PK

