



# MASTERColour CDM-TP

## MASTERC CDM-TP 70W/842 PG12-2 1CT/12

Range of protected, high-efficiency, discharge lamps with a stable color over lifetime and a crisp, sparkling light to be used in open luminaires

### Warnings and Safety

- Lamps may use electronic or electromagnetic control gear
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


General Information		Operating and Electrical	
Cap-Base	PG12-2 [PG12-2]	Power Consumption	73.2 W
Operating Position	UNIVERSAL [Any or Universal (U)]	Voltage (Nom)	90 V
Life to 50% Failures (Nom)	16,000 hour(s)	Voltage (Nom)	90 V
Light Technical		Controls and Dimming	
Color Code	842 [CCT of 4200K]	Dimmable	No
Color Designation	Cool White (CW)	Mechanical and Housing	
Chromaticity Coordinate X (Nom)	374	Bulb Finish	Clear
Chromaticity Coordinate Y (Nom)	378	Bulb Shape	T31 [T 31mm]
Correlated Color Temperature (Nom)	4200 K	Approval and Application	
Luminous Efficacy (rated) (Nom)	77 lm/W	Energy Efficiency Class	G
Color rendering index (CRI)	89	Mercury (Hg) Content (Nom)	7.1 mg
Arc Length O (Nom)	6 mm		

MASTERC colour CDM-TP

Energy Consumption kWh/1000 h	81 kWh
Product Data	
Order product name	MASTERC CDM-TP 70W/842 PG12-2 1CT/12
Full product name	MASTERC CDM-TP 70W/842 PG12-2 1CT/12
Full product code	871150020113315
Order code	928085909230


Material Nr. (12NC)	928085909230
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500201133
Numerator - Packs per outer box	12
EAN/UPC - Case	8711500201140

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)
MASTERC CDM-TP 70W/842 PG12-2 1CT/12	32.00 mm	6 mm	89 mm	93 mm	91 mm	149 mm

Lifetime



Lumen Maintenance Diagram - MASTERC CDM-TP 70W/842 PG12-2 1CT/12

