



CDM-SA/T



CDM-SA/T 150W/942 1CT/12

CDM-SA/T – the greener way to light up the night With a high luminous efficacy producing more lumens per watt than standard Architainment lamps, the CDM-SA/T is the greener alternative to light up the night. In addition, the optimal lamp filling and short arc of the lamp create a high beam intensity and excellent colour rendering.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap base	G12
Operating position	UNIVERSAL [Any or Universal (U)]
Flux measurement reference	Sphere
Life to 50% failures (nom.)	9,000 h
Light Technical	
Colour Code	942 [CCT of 4200K]
Luminous Flux	13,000 lm
Colour designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	0.371
Chromaticity Coordinate Y (Nom)	0.366
Correlated Colour Temperature	4200 K
Luminous efficacy (rated) (nom.)	84 lm/W
Colour rendering index (CRI)	95
Arc Length O (Nom)	6 mm


Operating and Electrical	
Power Consumption	155.0 W
Lamp current (nom.)	1.8 A
Controls and Dimming	
Dimmable	No
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) content (max.)	11.9 mg
Energy consumption kWh/1,000 hours	155 kWh
EPREL registration number	897559
Product Data	
Order product name	CDM-SA/T 150W/942 1CT/12
Full product name	CDM-SA/T 150W/942 1CT/12
Full EOC	871150020094515

CDM-SA/T

Order code	20094515
Material no. (12 NC)	928086605103
Local order code	150CDMTSA942
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500200945


Numerator – packs per outer box	12
EAN/UPC – Case	8711500200952

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
CDM-SA/T	20 mm	6	55 mm	57 mm	56	110 mm	31 mm	30	29 mm
150W/942		mm			mm			mm	
1CT/12									

Photometric data



Spectral Power Distribution Colour – CDM-SA/T 150W/942 1CT/12

