



# CDM

## CDM-SA/R 150W/942 UNP/1

The perfect color rendering and long life of these Ceramic Discharge Metal-halide lamps make them ideal for fiber optics lighting systems in shop displays, decorative lighting and swimming pool illumination. They can be mounted in color changing projectors.

### Product data


General Information	
Cap base	CERAMICAP-CABLE [ Ceramic Cap-Cable (C) ]
Operating position	UNIVERSAL [ Any or Universal (U) ]
Main application	Fiber Optics
Life to 50% failures (nom.)	6000 h
Light Technical	
Colour code	942 [ CCT of 4,200 K ]
Luminous flux (min.)	2200 lm
Luminous flux (nom.)	2650 lm
Colour designation	Cool White (CW)
Chromaticity coordinate X (nom.)	366
Chromaticity coordinate Y (nom.)	353
Correlated colour temperature (nom.)	4200 K
Luminous efficacy (rated) (nom.)	16.5 lm/W
Color rendering index (nom.)	96
Operating and Electrical	
Power (Rated) (Nom)	159 W
Lamp current (nom.)	1.76 A
Ignition supply voltage (min.)	198 V

Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Cap base information	Cable 250mm
Luminaire Design Requirements	
Bulb temperature (max.)	650 °C
Pinch temperature (max.)	350 °C
Product Data	
Full product code	871150020150800
Order product name	CDM-SA/R 150W/942 UNP/1
EAN/UPC – product	8727900783490
Order code	20150800
Numerator – quantity per pack	1
Numerator – packs per outer box	1
Material no. (12NC)	928086805303
Net weight (piece)	0.192 kg

### Warnings and Safety

# CDM

## Dimensional drawing





CDM-SA/R 150W/942

### Product

CDM-SA/R 150W/942 UNP/1

## Photometric data



XDPO\_XDCDMSAR\_942-Spectral power distribution Colour

