



MasterColor CDM-TM

CDM 35/TM/930

Introducing the smallest 20W ceramic metal halide lamp together with the unique e-Vision® electronic ballast. It's visually pleasing and financially rewarding, so the focus can be on your merchandise and not the ceiling clutter.

Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	PGJ5
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	12,000 hour(s)
Light Technical	
Color Code	930 [CCT of 3000K]
Color Designation	Warm White (WW)
Chromaticity Coordinate X (Nom)	0.436
Chromaticity Coordinate Y (Nom)	0.396
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	77 lm/W
Color rendering index (CRI)	91


Arc Length O (Nom)	4 mm
Operating and Electrical	
Power Consumption	39.1 W
Voltage (Nom)	96 V
Voltage (Nom)	96 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T13.3

MasterColor CDM-TM

Approval and Application	
Mercury (Hg) Content (Nom)	2.74 mg
Energy Consumption kWh/1000 h	43 kWh
Product Data	
Order product name	CDM 35/TM/930
Full product name	CDM 35/TM/930
Order code	211391


Material Nr. (12NC)	928093905115
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677211394
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677211399

Dimensional drawing




Product	D (max)	D	O	L (min)	L (max)	L	C (max)
CDM	9/16 inch	0.44	3/16	7/8 inch	15/16 inch	15/16	2-1/16 inch
35/TM/930		inch	inch			inch	

Photometric data




Light Distribution Diagram - CDM 35/TM/930




Spectral Power Distribution Colour - CDM 35/TM/930

Lifetime



Life Expectancy Diagram - CDM 35/TM/930



Lumen Maintenance Diagram - CDM 35/TM/930

