



MASTERColour CDM-T

MASTERC CDM-T 250W/942 G12 1CT/12

Range of single-ended, compact, high-efficiency, discharge lamps with a stable colour over lifetime and a crisp, sparkling light

Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Lamps may use electronic or electromagnetic control gear, except 35W/942 and 20W lamps, which must use electronic control gear.
- Lamps may use electronic or electromagnetic control gear, except 35W/942 and 20W lamps, which must use electronic control gear.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap-Base	G12 [G12]
Operating Position	UNIVERSAL [Any or Universal (U)]
Flux measurement reference	Sphere

Life to 50% Failures (Nom)	15,000 hour(s)
Light Technical	
Color Code	942 [CCT of 4200K]
Luminous Flux	26,250 lm

MASTERC colour CDM-T

Color Designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	0.371
Chromaticity Coordinate Y (Nom)	0.366
Correlated Color Temperature (Nom)	4200 K
Luminous Efficacy (rated) (Nom)	105 lm/W
Color rendering index (CRI)	91
Arc Length O (Nom)	12.3 mm

Operating and Electrical

Power Consumption	250.0 W
Voltage (Nom)	93 V
Voltage (Nom)	93 V

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Finish	Clear
Bulb Shape	T24 [T 24mm]


Approval and Application

Energy Efficiency Class	F
Mercury (Hg) Content (Max)	20 mg
Mercury (Hg) Content (Nom)	20.0 mg
Energy Consumption kWh/1000 h	250 kWh
EPREL Registration Number	473354

Product Data


Order product name	MASTERC CDM-T 250W/942 G12 1CT/12
Full product name	MASTERC CDM-T 250W/942 G12 1CT/12
Full product code	871150021112515
Order code	928094205131
Material Nr. (12NC)	928094205131
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500211125
Numerator - Packs per outer box	12
EAN/UPC - Case	8711500211132

Dimensional drawing




Product	D (max)	O	L (min)	L (max)	L	C (max)
MASTERC CDM-T 250W/942 G12 1CT/12	25 mm	12.3 mm	71.5 mm	73.5 mm	72.5 mm	135 mm

Photometric data




Light Distribution Diagram - MASTERC CDM-T 250W/942 G12 1CT/12




Spectral Power Distribution Colour - MASTERC CDM-T 250W/942 G12 1CT/12

MASTERC colour CDM-T

Lifetime



Lumen Maintenance Diagram - MASTERC CDM-T 250W/942 G12 1CT/12



Life Expectancy Diagram - MASTERC CDM-T 250W/942 G12 1CT/12

