



ML

ML 160W E27 225-235V SG 1SL/24

混合光线光源

安全提示


- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般信息	
底盖	E27 [E27]
操作位置	VBU/VBD30 [垂直或底座朝上/底座朝下 +/-30D]
50% 故障条件下的使用寿命 (标称)	8,000 小时
灯技术	
色度坐标 X (标称)	371
色度坐标 Y (标称)	380
相关色温 (标称)	3600 K
光效 (额定)(标称)	17 lm/W
显色指数 (CRI)	65
操作和电气	
功耗	165.0 W
电压 (标称)	230 V
电压 (标称)	230 V
控制和调光	
可调光	否
机械和外壳	
灯泡外观	镀膜玻璃


灯泡材料	软玻璃
灯泡外形	BF75 [BF 75 毫米]
审批和申请	
汞 (Hg) 含量 (标称)	13 mg
能耗 kWh/1000 h	160 kWh
产品数据	
订单产品名称	ML 160W E27 225-235V SG 1SL/24
完整的产品名称	ML 160W E27 225-235V SG 1SL/24
完整产品代码	871150018135030
订购代码	928095056891
材料编号 (12NC)	928095056891
计算器 - 每包数量	1
EAN/UPC - 产品/箱	8711500181350
计算器 - 每个外包装箱中的包数	24
EAN/UPC - 案例	8711500181367

二维绘图




Product	D (max)	C (max)
ML 160W E27 225-235V SG 1SL/24	76 mm	173 mm

光度数据




Spectral Power Distribution Colour - ML 160W E27 225-235V SG 1SL/24

寿命



Life Expectancy Diagram - ML 160W E27 225-235V SG 1SL/24



Lumen Maintenance Diagram - ML 160W E27 225-235V SG 1SL/24

