



MSD

MSD 200/2 1CT/4

MSD – right light, stage bright These single ended, compact lamps enable optimal light collection and accurate beam control, while they also provide true daylight colour temperatures – all to create great stage brightness and vivid entertainment. And since they offer long lifetime usage they help minimize the cost of ownership via fewer lamp replacements and fewer maintenance man hour costs.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Product data

General Information	
Cap-Base	GY9.5 [GY9.5]
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	3,000 h
Light Technical	
Color Code	670 (2)
Luminous Flux (Min)	11,340 lm
Luminous Flux	12,600 lm
Chromaticity Coordinate X (Nom)	313
Chromaticity Coordinate Y (Nom)	315
Correlated Color Temperature (Nom)	6600 K
Luminous Efficacy (rated) (Nom)	63 lm/W
Color rendering index (CRI)	70
Arc Length O (Nom)	5.0 mm

Operating and Electrical	
Power Consumption	200 W
Lamp Current (Nom)	3.4 A
Controls and Dimming	
Dimmable	No
Product Data	
Order product name	MSD 200/2 1CT/4
Full product name	MSD 200/2 1CT/4
Full product code	871869641590000
Local code description	MSD2002
Order code	928097605115
Material Nr. (12NC)	928097605115
Local order code	MSD2002
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696415900


Numerator - Packs per outer box	4
EAN/UPC - Case	8718696415917

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSD 200/2	23 mm	5.0	54 mm	56 mm	55	108 mm	29 mm	28	27 mm
1CT/4		mm			mm			mm	

Photometric data



Spectral Power Distribution Colour - MSD 200/2 1CT/4

