



MSR Hot Restrike

MSR 575 HR 1CT/4

Thanks to an optimized color temperature and a high color rendering index, the MSR Hot Restrike creates perfect 'daylight' in any condition. Also, the single ended lamp design enables hot re-ignition, which ensures daylight lighting and superb color rendition is always instantly available. They also incorporate the innovative P3 technology, developed by Philips, which allows use at higher temperatures and therefore extends lifetime and consistency of high-quality light output.


Product data

General Information	
Base	G22 [G22]
Operating Position	Universal [Universal]
Main Application	Studio/Theatre
Life to 50% Failures (Nom)	1000 h
System Description	Hot Restrike
Light Technical	
Color Code	- [Not Specified]
Initial lumen (Min)	43200 lm
Initial lumen (Nom)	48000 lm
Chromaticity Coordinate X (Nom)	323
Chromaticity Coordinate Y (Nom)	328
Correlated Color Temperature (Nom)	6000 K
Luminous Efficacy (Rated) (Min)	75 lm/W
Luminous Efficacy (rated) (Nom)	83 lm/W
Color Rendering Index (Nom)	90
Operating and Electrical	
Power (Rated) (Nom)	575 W
Lamp Current (Nom)	6.75 A

Ignition Supply Voltage (Min)	207 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Cap-Base Information	na [-]
Luminaire Design Requirements	
Bulb Temperature (Max)	700 °C
Pinch Temperature (Max)	350 °C
Product Data	
Order product name	MSR 575 HR 1CT/4
EAN/UPC - Product	8718291221050
Order code	287276
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	928097705115
Net Weight (Piece)	0.100 kg

Warnings and Safety



Dimensional drawing



MSR 575 HR

Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSR 575	30 mm	7.0	69 mm	71 mm	70	145 mm	43 mm	42	41 mm
HR 1CT/4		mm			mm			mm	

Photometric data



XDPO_XDMSR_HR--Spectral power distribution Colour

