# **PHILIPS** Lighting



# **MSR Hot Restrike**

## MSR 575 HR 1CT/4

Thanks to an optimized color temperature and a high color rendering index, the MSR Hot Restrike creates perfect 'daylight' in any condition. Also, the single ended lamp design enables hot re-ignition, which ensures daylight lighting and superb color rendition is always instantly available. They also incorporate the innovative P3 technology, developed by Philips, which allows use at higher temperatures and therefore extends lifetime and consistency of high-quality light output.

#### Warnings and Safety

• A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

#### **Product data**


General Information					
Cap-Base	G22 UNIVERSAL [Any or Universal (U)]				
Operating Position					
Life to 50% Failures (Nom)	1,000 hour(s)				
Light Technical					
Color Code	- [Not Specified]				
Luminous Flux (Min)	43,200 lm 48,000 lm				
Luminous Flux					
Chromaticity Coordinate X (Nom)	323				
Chromaticity Coordinate Y (Nom)	328				
Correlated Color Temperature (Nom)	6000 K				
Luminous Efficacy (Rated) (Min)	75 lm/W				
Luminous Efficacy (rated) (Nom)	83 lm/W				
Color rendering index (CRI)	90				

Arc Length O (Nom)	7.0 mm				
Operating and Electrical					
Power Consumption	575 W				
Lamp Current (Nom)	6.75 A				
Controls and Dimming					
Dimmable	Yes				
Product Data					
Order product name	MSR 575 HR 1CT/4				
Full product name	MSR 575 HR 1CT/4				
Full product code	871829122105000				
Order code	928097705115				
Material Nr. (12NC)	928097705115				
Numerator - Quantity Per Pack	1				

### **MSR Hot Restrike**


EAN/UPC - Product/Case	8718291221050				
Numerator - Packs per outer box	4				
EAN/UPC - Case	8718291221067				

#### **Dimensional drawing**



Product	D (max)	0	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSR 575	30 mm	7.0	69 mm	71 mm	70	145 mm	43 mm	42	41 mm
HR 1CT/4		mm			mm			mm	
HR 1CT/4		mm			mm			mm	

#### Photometric data



Spectral Power Distribution Colour - MSR 575 HR 1CT/4



© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2024, January 18 - data subject to change