



MSD

MSD 250 1CT/4

These single ended, compact lamps enable optimal light collection and accurate beam control, while they also provide true daylight color temperatures – all to create great stage brightness and vivid entertainment. And since they offer long lifetime usage they help minimize the cost of ownership via fewer lamp replacements and fewer maintenance man hour costs.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data


| General Information | |
|------------------------------------|----------------------------------|
| Cap-Base | GY9.5 [GY9.5] |
| Operating Position | UNIVERSAL [Any or Universal (U)] |
| Life to 50% Failures (Nom) | 3,000 hour(s) |
| Light Technical | |
| Color Code | - [Not Specified] |
| Luminous Flux (Min) | 15,000 lm |
| Luminous Flux | 18,000 lm |
| Chromaticity Coordinate X (Nom) | 312 |
| Chromaticity Coordinate Y (Nom) | 311 |
| Correlated Color Temperature (Nom) | 6700 K |
| Luminous Efficacy (rated) (Nom) | 72 lm/W |
| Color rendering index (CRI) | 75 |

| Arc Length O (Nom) | 5.0 mm |
|--------------------------|-----------------|
| Operating and Electrical | |
| Power Consumption | 250 W |
| Lamp Current (Nom) | 3 A |
| Controls and Dimming | |
| Dimmable | No |
| Product Data | |
| Order product name | MSD 250 1CT/4 |
| Full product name | MSD 250 1CT/4 |
| Full product code | 871869641588700 |
| Order code | 261420 |

| | |
|---------------------------------|---------------|
| Material Nr. (12NC) | 928098705115 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8718696415887 |
| Numerator - Packs per outer box | 4 |


| | |
|----------------|---------------|
| EAN/UPC - Case | 8718696415894 |
|----------------|---------------|

Dimensional drawing



| Product | D (max) | O | L (min) | L (max) | L | C (max) | F (max) | F | F (min) |
|---------|------------|------|---------|------------|--------|------------|---------|-------|---------|
| MSD 250 | 15/16 | 1/4 | 2-1/8 | 2-1/4 | 2-3/16 | 4-1/4 | 1-3/16 | 1-1/8 | 1-1/16 |
| 1CT/4 | inch | inch | inch | inch | inch | inch | inch | inch | inch |

Photometric data



Spectral Power Distribution Colour - MSD 250 1CT/4

