



# MSD

## MSD 250/2 30H 1CT/4

MSD – right light, stage bright These single ended, compact lamps enable optimal light collection and accurate beam control, while they also provide true daylight colour temperatures – all to create great stage brightness and vivid entertainment. And since they offer long lifetime usage they help minimize the cost of ownership via fewer lamp replacements and fewer maintenance man hour costs.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


General Information	
Cap-Base	GY9.5 [GY9.5]
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	3,000 hour(s)
Light Technical	
Color Code	850 [CCT of 5000K]
Luminous Flux (Min)	16,000 lm
Luminous Flux	18,000 lm
Chromaticity Coordinate X (Nom)	289
Chromaticity Coordinate Y (Nom)	305
Correlated Color Temperature (Nom)	8100 K
Luminous Efficacy (rated) (Nom)	72 lm/W
Color rendering index (CRI)	70

Arc Length O (Nom)	5.0 mm
Operating and Electrical	
Power Consumption	250 W
Lamp Current (Nom)	3 A
Controls and Dimming	
Dimmable	No
Product Data	
Order product name	MSD 250/2 30H 1CT/4
Full product name	MSD 250/2 30H 1CT/4
Full product code	871829122806600
Order code	928099005115

Material Nr. (12NC)	928099005115
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291228066
Numerator - Packs per outer box	4


EAN/UPC - Case	8718291228073
----------------	---------------

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSD 250/2	23 mm	5.0	54 mm	56 mm	55	108 mm	29 mm	28	27 mm
30H 1CT/4		mm			mm			mm	

Photometric data



Spectral Power Distribution Colour - MSD 250/2 30H 1CT/4

