



MASTER MHN-SA

MASTER MHN-SA 1800W/956 230V XW UNP/1

Compact quartz metal halide lamps with double-pinch

Product data

General Information	
Cap base	X830R [X830R]
Operating position	P15 [Parallel +/-15D or Horizontal(HOR)]
Life to 5% failures (nom.)	1800 h
Life to 10% failures (nom.)	2300 h
Life to 20% failures (nom.)	3000 h
Life to 50% failures (nom.)	5000 h
Light Technical	
Colour code	956 [CCT of 5,600 K]
Luminous flux (rated) (nom.)	155000 lm
Colour designation	Daylight
Lumen maintenance 1,000 hours (nom.)	92 %
Lumen maintenance 2,000 hours (nom.)	80 %
Lumen maintenance 5,000 hours (nom.)	60 %
Chromaticity coordinate X (nom.)	330
Chromaticity coordinate Y (nom.)	339
Correlated colour temperature (nom.)	5600 K
Luminous efficacy (rated) (nom.)	86 lm/W
Color rendering index (nom.)	86
Operating and Electrical	
Lamp supply voltage	230 V [230]
Power (Rated) (Nom)	1800.0 W
Lamp current run-up (max.)	25 A
Lamp current (EM) (nom.)	17.3 A

Ignition supply voltage (min.)	198 V
Voltage (Max)	130 V
Voltage (Min)	110 V
Voltage (Nom)	120 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb finish	Clear
Cap base information	na [-]
Approval and Application	
Energy efficiency label (EEL)	A+
Mercury (Hg) content (nom.)	92 mg
Energy Consumption kWh/1000 h	1980 kWh
Luminaire Design Requirements	
Bulb temperature (max.)	980 °C
Pinch temperature (max.)	300 °C
Product Data	
Full product code	871150020106500
Order product name	MASTER MHN-SA 1800W/956 230V XW UNP/1
EAN/UPC – product	8718291548294
Order code	20106500


MASTER MHN-SA

Numerator – quantity per pack	1
Numerator – packs per outer box	1
Material no. (12NC)	928099205130
Net weight (piece)	110.000 g

ILCOS Code	MN-1800-H-X830R-/H
------------	--------------------

Warnings and Safety

Dimensional drawing




MHN-SA 1800W/956 230V XW


Product

MASTER MHN-SA 1800W/956 230V XW UNP/1


Photometric data



Lifetime



MHN SA 1800W 956 Life Expectancy Diagram



MHN SA 1800W 956 Lumen Maintenance Diagram

