



Architectural MSA

MSA 2500 DE UNP/1

The high luminous efficacy and optimal lamp filling of the double ended Architectural MSA lamps create high beam intensity and excellent color rendering. While the compact arc of the lamp allows efficient beam control and high intensity. Ideal to illuminate architecture of all types at night.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


Product data

General Information		Operating and Electrical	
Cap-Base	(P)SFC [(P)SFC]	Power Consumption	2,500 W
Operating Position	P15 [Parallel +/-15D or Horizontal(HOR)]	Lamp Current (Nom)	22.5 A
Life to 50% Failures (Nom)	2,500 hour(s)		
Light Technical		Controls and Dimming	
Color Code	856	Dimmable	No
Luminous Flux	250,000 lm		
Chromaticity Coordinate X (Nom)	330	Product Data	
Chromaticity Coordinate Y (Nom)	360	Order product name	MSA 2500 DE UNP/1
Correlated Color Temperature (Nom)	5600 K	Full product name	MSA 2500 DE UNP/1
Luminous Efficacy (rated) (Nom)	100 lm/W	Full product code	871150020208600
Color rendering index (CRI)	88	Order code	928099405103
Arc Length O (Nom)	25 mm	Material Nr. (12NC)	928099405103
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8718291548300

Architectural MSA


Numerator - Packs per outer box	1
EAN/UPC - Case	8711500202086

Dimensional drawing



Product	D (max)	O	C (max)
MSA 2500 DE UNP/1	41 mm	25 mm	364 mm

Photometric data



Spectral Power Distribution Colour - MSA 2500 DE UNP/1

