



MSR Gold™ SA Double Ended

MSR Gold™ 1200 SA/DE 1CT/4

To optimize the total lifetime of the double ended MSR Gold™ SA Double Ended lamps, the caps are plated with gold. This provides superior heat protection and thereby minimizes premature failure of the lamp and lamp holder, as well as ensuring extended consistent performance. In addition, the highly innovative P3 technology, developed by Philips, allows the lamp to be used at higher temperatures, which further extends service life and consistency of high-quality light output.

Product data

General Information	
Base	SFC10-4 [SFC10-4]
Operating Position	Universal [Universal]
Main Application	Entertainment
Life to 50% Failures (Nom)	750 h
System Description	SA/DE

Light Technical	
Color Code	- [Not Specified]
Initial lumen (Min)	92700 lm
Initial lumen (Nom)	103000 lm
Chromaticity Coordinate X (Nom)	326
Chromaticity Coordinate Y (Nom)	332
Correlated Color Temperature (Nom)	6000 K
Luminous Efficacy (Rated) (Min)	77 lm/W
Luminous Efficacy (rated) (Nom)	86 lm/W
Color Rendering Index (Nom)	85

Operating and Electrical	
Power (Rated) (Nom)	1200 W
Lamp Current (Nom)	13.6 A
Ignition Supply Voltage (Min)	198 V

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Cap-Base Information	SFC10-4

Product Data	
Order product name	MSR Gold™ 1200 SA/DE 1CT/4
EAN/UPC - Product	8718291221210
Order code	287144
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	928099605115

MSR Gold™ SA Double Ended


Net Weight (Piece)

34.000 g

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050



Dimensional drawing



Product	D (max)	O	A (min)	A (max)	A	C (max)
MSR Gold™ 1200 SA/DE 1CT/4	22 mm	7.0 mm	114.4 mm	115.2 mm	114.8 mm	136 mm

MSR GOLD 1200 SA/DE

Photometric data



XDPO_XDMSR_SADE-Spectral power distribution Colour

