



MSR Hot Restrike

MSR 1200 HR 1CT/2

Thanks to an optimized color temperature and a high color rendering index, the MSR Hot Restrike creates perfect 'daylight' in any condition. Also, the single ended lamp design enables hot re-ignition, which ensures daylight lighting and superb color rendition is always instantly available. They also incorporate the innovative P3 technology, developed by Philips, which allows use at higher temperatures and therefore extends lifetime and consistency of high-quality light output.

Warnings and Safety

• A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information					
Cap-Base	G38 [G38]				
Operating Position	UNIVERSAL [Any or Universal (U)]				
Life to 50% Failures (Nom)	1,000 hour(s)				
Light Technical					
Color Code	- [Not Specified]				
Luminous Flux	103,000 lm				
Chromaticity Coordinate X (Nom)	323				
Chromaticity Coordinate Y (Nom)	328				
Correlated Color Temperature (Nom)	6000 K				
Luminous Efficacy (Rated) (Min)	75 lm/W				
Luminous Efficacy (rated) (Nom)	88 lm/W				
Color rendering index (CRI)	95				
Arc Length O (Nom)	10.0 mm				


Operating and Electrical				
Power Consumption	1,200 W			
Lamp Current (Nom)	13.5 A			
Controls and Dimming				
Dimmable	Yes			
Product Data				
Order product name	MSR 1200 HR 1CT/2			
Full product name	MSR 1200 HR 1CT/2			
Full product code	872790092606400			
Order code	928105005114			
Material Nr. (12NC)	928105005114			
Numerator - Quantity Per Pack	1			
EAN/UPC - Product/Case	8727900926064			
Numerator - Packs per outer box	2			

Datasheet, 2023, April 14 data subject to change

EAN/UPC - Case


8727900926071

Dimensional drawing



Product	D (max)	0	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSR 1200	40 mm	10.0	106	108 mm	107	200	67 mm	65	63 mm
HR 1CT/2		mm	mm		mm	mm		mm	

Photometric data



Spectral Power Distribution Colour - MSR 1200 HR 1CT/2



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.