PHILIPS Lighting



MSR Hot Restrike

MSR 1200 HR 1CT/2

Thanks to an optimized color temperature and a high color rendering index, the MSR Hot Restrike creates perfect 'daylight' in any condition. Also, the single ended lamp design enables hot re-ignition, which ensures daylight lighting and superb color rendition is always instantly available. They also incorporate the innovative P3 technology, developed by Philips, which allows use at higher temperatures and therefore extends lifetime and consistency of high-quality light output.

Warnings and Safety

• A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information					
Cap-Base	G38				
Operating Position	UNIVERSAL [Any or Universal (U)]				
Life to 50% Failures (Nom)	1,000 hour(s)				
Light Technical					
Color Code	- [Not Specified]				
Luminous Flux	103,000 lm				
Chromaticity Coordinate X (Nom)	323 328				
Chromaticity Coordinate Y (Nom)					
Correlated Color Temperature (Nom)	6000 K				
Luminous Efficacy (Rated) (Min)	75 lm/W				
Luminous Efficacy (rated) (Nom)	88 lm/W				
Color rendering index (CRI)	95				
Arc Length O (Nom)	10.0 mm				


Operating and Electrical					
Power Consumption	1,200 W				
Lamp Current (Nom)	13.5 A				
Controls and Dimming					
Dimmable	Yes				
Product Data					
Order product name	MSR 1200 HR 1CT/2				
Full product name	MSR 1200 HR 1CT/2				
Full product code	872790092606400				
Order code	928105005114				
Material Nr. (12NC)	928105005114				
Numerator - Quantity Per Pack	1				
EAN/UPC - Product/Case	8727900926064				
Numerator - Packs per outer box	2				

MSR Hot Restrike

EAN/UPC - Case

8727900926071

Dimensional drawing



Product	D (max)	0	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSR 1200	40 mm	10.0	106	108 mm	107	200	67 mm	65	63 mm
HR 1CT/2		mm	mm		mm	mm		mm	

Photometric data

Spectral Power Distribution Colour - MSR 1200 HR 1CT/2



© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2024, January 19 - data subject to change