

PHILIPS

Lighting



MSR

MSR 1200/2 1CT/3

The high color rendering index of the single ended MSR series ensures that everyone in the audience can enjoy the true colors of the scenery, the stage props, the players and their costumes – in fact everything that is on stage can be made bright and vivid in daylight quality light. Also, thanks to the single ended lamp concept, the luminaire has optimal light collection and direction possibilities to help ensure brightness on stage exactly where and when it is needed. In addition, the MSR can be used in any burning position for easy set-up and convenience.

Product data


General Information		Ignition supply voltage (min.)		207 V	
Cap base	G22 [G22]				
Operating position	UNIVERSAL [Any or Universal (U)]				
Main application	Studio/Disco				
Life to 50% failures (nom.)	800 h				
System description	Cold Strike				
Light Technical		Controls and Dimming			
Colour code	2	Dimmable	No		
Luminous flux (min.)	93600 lm				
Luminous flux (nom.)	104000 lm				
Chromaticity coordinate X (nom.)	302				
Chromaticity coordinate Y (nom.)	320				
Correlated colour temperature (nom.)	7200 K				
Luminous efficacy (rated) (nom.)	87 lm/W				
Color rendering index (nom.)	85				
Operating and Electrical		Mechanical and Housing			
Power (Rated) (Nom)	1200 W	Cap base information	30x53mm		
Lamp current (nom.)	13.8 A				
		Luminaire Design Requirements			
		Bulb temperature (max.)	700 °C		
		Pinch temperature (max.)	350 °C		
		Product Data			
		Full product code	872790091133600		
		Order product name	MSR 1200/2.1CT/3		
		EAN/UPC – product	8727900911336		
		Order code	91133600		
		Numerator – quantity per pack	1		
		Numerator – packs per outer box	3		
		Material no. (12NC)	928171805114		

MSR

Net weight (piece)	0.150 kg
--------------------	----------

Warnings and Safety

Dimensional drawing



MSR 1200/2

Product

MSR 1200/2.1CT/3

Photometric data

