



MSR Short Arc

MSR 2000 SA 1CT/8

The lamp's short arc and compact design helps enable a compact luminaire that provides high beam intensity, while the excellent color rendition characteristics help ensure optimal colors on stage. The highly innovative P3 technology, developed by Philips, allows MSR Short Arc lamps to be used at higher temperatures in any burning position. The result? Longer lifetime, fewer early failures and a highly consistent performance throughout the lamp's lifetime.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data


General Information		Arc Length O (Nom)	
Cap-Base	GY22	7.0 mm	
Operating Position	UNIVERSAL [Any or Universal (U)]	Operating and Electrical	
Life to 50% Failures (Nom)	750 hour(s)	Power Consumption	2,000 W
Light Technical		Lamp Current (Nom)	21.5 A
Color Code	- [Not Specified]	Controls and Dimming	
Luminous Flux	174,000 lm	Dimmable	Yes
Chromaticity Coordinate X (Nom)	323	Product Data	
Chromaticity Coordinate Y (Nom)	334	Order product name	MSR 2000 SA 1CT/8
Correlated Color Temperature (Nom)	6000 K	Full product name	MSR 2000 SA 1CT/8
Luminous Efficacy (rated) (Nom)	87 lm/W	Full product code	872790091573000
Color rendering index (CRI)	85		

MSR Short Arc

Order code	245415
Material Nr. (12NC)	928173205114
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900915730


Numerator - Packs per outer box	8
EAN/UPC - Case	8727900915747

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)
MSR 2000 SA 1CT/8	1-3/8 inch	5/16 inch	2-5/16 inch	2-3/8 inch	2-3/8 inch	5-5/16 inch

Photometric data



Spectral Power Distribution Colour - MSR 2000 SA 1CT/8

