



MSR Gold™ SA Double Ended

MSR Gold™ 700 SA/2 DE 1CT/4

To optimize the total lifetime of the double ended MSR Gold™ SA Double Ended lamps, the caps are plated with gold. This provides superior heat protection and thereby minimizes premature failure of the lamp and lamp holder, as well as ensuring extended consistent performance. In addition, the highly innovative P3 technology, developed by Philips, allows the lamp to be used at higher temperatures, which further extends service life and consistency of high-quality light output.

Product data

| General Information | | Color Rendering Index (Nom) | |
|------------------------------------|------------------------|-------------------------------|-----------------------------|
| Base | SFC10-4 [SFC10-4] | | 75 |
| Operating Position | Universal [Universal] | Operating and Electrical | |
| Main Application | Studio/Disco | Power (Rated) (Nom) | 700 W |
| Life to 50% Failures (Nom) | 750 h | Lamp Current (Nom) | 11.5 A |
| System Description | SA/2 DE | Ignition Supply Voltage (Min) | 198 V |
| Light Technical | | Controls and Dimming | |
| Color Code | - [Not Specified] | Dimmable | No |
| Initial lumen (Min) | 43200 lm | Mechanical and Housing | |
| Initial lumen (Nom) | 48000 lm | Cap-Base Information | SFC10-4 |
| Chromaticity Coordinate X (Nom) | 299 | Luminaire Design Requirements | |
| Chromaticity Coordinate Y (Nom) | 320 | Pinch Temperature (Max) | 500 °C |
| Correlated Color Temperature (Nom) | 7500 K | Product Data | |
| Luminous Efficacy (Rated) (Min) | 62 lm/W | Order product name | MSR Gold™ 700 SA/2 DE 1CT/4 |
| Luminous Efficacy (rated) (Nom) | 69 lm/W | | |
| Color Rendering Index (Min) | 62 | | |

MSR Gold™ SA Double Ended


| | |
|---------------------------------|---------------|
| EAN/UPC - Product | 8718291221234 |
| Order code | 287136 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 4 |

| | |
|---------------------|--------------|
| Material Nr. (12NC) | 928174705115 |
| Net Weight (Piece) | 34.000 g |

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury. Manage in Accord with Disposal Laws. See: www.lamprecycle.org or 1-800-555-0050



Dimensional drawing



| Product | D (max) | O | A (min) | A (max) | A | C (max) |
|-----------------------------|---------|--------|----------|----------|----------|---------|
| MSR Gold™ 700 SA/2 DE 1CT/4 | 19 mm | 4.0 mm | 114.4 mm | 115.2 mm | 114.8 mm | 136 mm |

MSR GOLD 700 SA/2 DE

Photometric data



XDPO_XDMSR_700W_SA2-DE-Spectral power distribution Colour

MSR Gold™ SA Double Ended

