



MSR Gold™ FastFit

MSR Gold 1200 FastFit 1CT/4

All lamps burn out eventually, but when this happens with single ended MSR Gold™ FastFit, it is replaced in seconds – thanks to the specially designed lamp base and lamp holder. This lamp provides a high beam intensity of pure, white light for a truly illuminating performance, while the gold-plated caps provide superior heat protection and prevent premature failure. P3 technology allows use in any position and at higher temperatures, further extending lamp life and consistency of high-quality light output. Also, because the FastFit design is applied to Philips Halogen lamps, switching between lamp technologies can be done quickly and easily. The Philips MSR GoldTM 1200 FastFit can be operated in a lamp wattage range between 800W and 1400W.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Color rendering index (CRI)	
Cap-Base	PGJX50 [PGJX50]	Arc Length O (Nom)	5.5 mm
Operating Position	UNIVERSAL [Any or Universal (U)]	Operating and Electrical	
Life to 50% Failures (Nom)	750 hour(s)	Power Consumption	1,200 W
Light Technical		Lamp Current (Nom)	15 A
Color Code	- [Not Specified]	Controls and Dimming	
Luminous Flux	100,000 lm	Dimmable	Yes
Chromaticity Coordinate X (Nom)	318	Product Data	
Chromaticity Coordinate Y (Nom)	327	Order product name	MSR Gold 1200 FastFit 1CT/4
Correlated Color Temperature (Nom)	6000 K		
Luminous Efficacy (rated) (Nom)	83 lm/W		

MSR Gold™ FastFit

Full product name	MSR Gold 1200 FastFit 1CT/4
Full product code	871829122129600
Order code	928175005115
Material Nr. (12NC)	928175005115
Numerator - Quantity Per Pack	1

EAN/UPC - Product/Case	8718291221296
Numerator - Packs per outer box	4
EAN/UPC - Case	8718291221302

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F
MSR Gold 1200 FastFit 1CT/4	26.1 mm	5.5 mm	64 mm	66 mm	65 mm	128 mm	50 mm

