



MSR Gold™ FastFit

MSR Gold 1200 FastFit 1CT/4

All lamps burn out eventually, but when this happens with single ended MSR Gold™ FastFit, it is replaced in seconds – thanks to the specially designed lamp base and lamp holder. This lamp provides a high beam intensity of pure, white light for a truly illuminating performance, while the gold-plated caps provide superior heat protection and prevent premature failure. P3 technology allows use in any position and at higher temperatures, further extending lamp life and consistency of high-quality light output. Also, because the FastFit design is applied to Philips Halogen lamps, switching between lamp technologies can be done quickly and easily. The Philips MSR GoldTM FastFit can be operated in a lamp wattage range between 700W and 2500W.

Warnings and Safety

• A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

Cap-Base PGJX50 Operating Position UNIVERSAL [Any or Universal (U)] Life to 50% Failures (Nom) 750 hour(s) Light Technical Color Code - [Not Specified] Luminous Flux 100,000 lm Chromaticity Coordinate X (Nom) 318 Chromaticity Coordinate Y (Nom) 327	General Information				
Light Technical Color Code - [Not Specified] Luminous Flux 100,000 lm Chromaticity Coordinate X (Nom) 318	Cap-Base	PGJX50			
Light Technical Color Code - [Not Specified] Luminous Flux 100,000 lm Chromaticity Coordinate X (Nom) 318	Operating Position	UNIVERSAL [Any or Universal (U)]			
Color Code - [Not Specified] Luminous Flux 100,000 lm Chromaticity Coordinate X (Nom) 318	Life to 50% Failures (Nom)	750 hour(s)			
Color Code - [Not Specified] Luminous Flux 100,000 lm Chromaticity Coordinate X (Nom) 318					
Luminous Flux 100,000 lm Chromaticity Coordinate X (Nom) 318	Light Technical				
Chromaticity Coordinate X (Nom) 318	Color Code	- [Not Specified]			
	Luminous Flux	100,000 lm			
Chromaticity Coordinate Y (Nom) 327	Chromaticity Coordinate X (Nom)	318			
	Chromaticity Coordinate Y (Nom)	327			
Correlated Color Temperature (Nom) 6000 K	Correlated Color Temperature (Nom)	6000 K			
Luminous Efficacy (rated) (Nom) 83 lm/W	Luminous Efficacy (rated) (Nom)	83 lm/W			

Color rendering index (CRI)	80					
Arc Length O (Nom)	5.5 mm					
Operating and Electrical						
Power Consumption	1,200 W					
Lamp Current (Nom)	15 A					
Controls and Dimming						
Dimmable	Yes					
Product Data						
Order product name	MSR Gold 1200 FastFit 1CT/4					


Datasheet, 2024, February 8 data subject to change

MSR Gold™ FastFit

Full product name	MSR Gold 1200 FastFit 1CT/4			
Full product code	871829122129600			
Order code	928175005115			
Material Nr. (12NC)	928175005115			
Numerator - Quantity Per Pack	1			

EAN/UPC - Product/Case	8718291221296	
Numerator - Packs per outer box	4	
EAN/UPC - Case	8718291221302	

Dimensional drawing



Product	D (max)	0	L (min)	L (max)	L	C (max)	F
MSR Gold 1200 FastFit	26.1 mm	5.5 mm	64 mm	66 mm	65 mm	128 mm	50 mm
1CT/4							

