

**PHILIPS**

Lighting



# MSR Gold™ SA Double Ended

## MSR Gold™ 575 SA/2 DE 1CT/40

To optimize the total lifetime of the double ended MSR Gold™ SA Double Ended lamps, the caps are plated with gold. This provides superior heat protection and thereby minimizes premature failure of the lamp and lamp holder, as well as ensuring extended consistent performance. In addition, the highly innovative P3 technology, developed by Philips, allows the lamp to be used at higher temperatures, which further extends service life and consistency of high-quality light output.

### Product data

General Information	
Cap base	SFC-11 [ SFC-11]
Burning Position	UNIVERSAL [ Any/Universal]
Main application	Entertainment
Life to 50% failures (nom.)	750 h
System description	SA/2 DE

Light Technical	
Colour Code	2
Lamp Luminous Flux 25°C EL (Min)	39000 lm
Lamp Luminous Flux 25°C EL (Nom)	42000 lm
Chromaticity coordinate X (nom.)	294
Chromaticity coordinate Y (nom.)	317
Colour Temperature, horizontal (Nom)	7500 K
Lamp Luminous Efficacy EM (Nom)	73 lm/W
Colour Rendering Index,horiz (Nom)	75

Operating and Electrical	
Power (Rated) (Nom)	575 W
Lamp current (nom.)	7 A
Ignition supply voltage (min.)	198 V

Controls and Dimming	
Dimmable	no

Mechanical and Housing	
Cap base information	SFC-11

Luminaire Design Requirements	
Pinch temperature (max.)	400 °C

Product Data	
Full product code	872790091464100
Order product name	MSR Gold™ 575 SA/2 DE 1CT/40
EAN/UPC – product	8727900914641


## MSR Gold™ SA Double Ended

Order code	928175105114
Local Code	MSRG575SA/2DE
Numerator – quantity per pack	1
Numerator – packs per outer box	40

Material no. (12NC)	928175105114
Net weight (piece)	0.032 kg

### Warnings and Safety



### Dimensional drawing



MSR GOLD 575 SA/2 DE

Product	D (max)	O	A (min)	A (max)	A	C (max)
MSR Gold™ 575 SA/2 DE	18.5 mm	5.0 mm	69.6 mm	70.4 mm	70 mm	92 mm
1CT/40						

### Photometric data



XDPB\_XDMSR\_575W\_SA2-DE-Spectral power distribution B/W

