



# MSR Hot Restrike

## MSR 250 HR 1CT/4

Thanks to an optimized color temperature and a high color rendering index, the MSR Hot Restrike creates perfect 'daylight' in any condition. Also, the single ended lamp design enables hot re-ignition, which ensures daylight lighting and superb color rendition is always instantly available. They also incorporate the innovative P3 technology, developed by Philips, which allows use at higher temperatures and therefore extends lifetime and consistency of high-quality light output.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

### Product data


General Information		Color rendering index (CRI)	
Cap-Base	GZY9.5 [GZY9.5]	Arc Length O (Nom)	90
Operating Position	UNIVERSAL [Any or Universal (U)]		5.0 mm
Life to 50% Failures (Nom)	750 hour(s)	Operating and Electrical	
Light Technical		Power Consumption	250 W
Color Code	- [Not Specified]	Lamp Current (Nom)	2.6 A
Luminous Flux (Min)	18,500 lm	Controls and Dimming	
Luminous Flux	20,000 lm	Dimmable	No
Chromaticity Coordinate X (Nom)	309	Product Data	
Chromaticity Coordinate Y (Nom)	320	Order product name	MSR 250 HR 1CT/4
Correlated Color Temperature (Nom)	6000 K	Full product name	MSR 250 HR 1CT/4
Luminous Efficacy (rated) (Nom)	80 lm/W		

MSR Hot Restrike

Full product code	871869641602000
Order code	261370
Material Nr. (12NC)	928175605115
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696416020


Numerator - Packs per outer box	4
EAN/UPC - Case	8718696416037

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSR 250	15/16	1/4	2-5/16	2-3/8	2-3/8	4-3/8	1 inch	15/16	15/16
HR 1CT/4	inch	inch	inch	inch	inch	inch		inch	inch

Photometric data



Spectral Power Distribution Colour - MSR 250 HR 1CT/4

