



MSR Gold™ SA Double Ended

MSR GOLD 1510 SA/DE BULK

To optimize the total lifetime of the double ended MSR Gold™ SA Double Ended lamps, the caps are plated with gold. This provides superior heat protection and thereby minimizes premature failure of the lamp and lamp holder, as well as ensuring extended consistent performance. In addition, the highly innovative P3 technology, developed by Philips, allows the lamp to be used at higher temperatures, which further extends service life and consistency of high-quality light output.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information		Operating and Electrical	
Cap-Base	SFC10-4 [SFC10-4]	Correlated Color Temperature (Nom)	6000 K
Operating Position	UNIVERSAL [Any or Universal (U)]	Luminous Efficacy (rated) (Nom)	93 lm/W
Life to 50% Failures (Nom)	750 hour(s)	Color rendering index (CRI)	85
		Arc Length O (Nom)	7.0 mm
Light Technical			
Color Code	- [Not Specified]	Power Consumption	1,510 W
Luminous Flux	140,000 lm	Lamp Current (Nom)	13.5 A
Chromaticity Coordinate X (Nom)	326		
Chromaticity Coordinate Y (Nom)	336		

MSR Gold™ SA Double Ended

Controls and Dimming

Dimmable Yes

Product Data

Order product name	MSR Gold 1510 SA/DE UNP/108
Full product name	MSR GOLD 1510 SA/DE BULK
Full product code	871150021342629
Order code	207829

Material Nr. (12NC) 928176605112


Numerator - Quantity Per Pack 1

EAN/UPC - Product/Case 8711500213426

Numerator - Packs per outer box 108


EAN/UPC - Case 8711500213433

Dimensional drawing



Product	D (max)	O	A	C (max)
MSR Gold 1510 SA/DE UNP/108	15/16 inch	5/16 inch	4-9/16 inch	5-3/8 inch

Photometric data



Spectral Power Distribution Colour - MSR Gold 1510 SA/DE UNP/108

