



MSR Gold™ FastFit

MSR Gold™ 2000 FastFit 1CT/8

All lamps burn out eventually, but when this happens with single ended MSR Gold™ FastFit, it is replaced in seconds – thanks to the specially designed lamp base and lamp holder. This lamp provides a high beam intensity of pure, white light for a truly illuminating performance, while the gold-plated caps provide superior heat protection and prevent premature failure. P3 technology allows use in any position and at higher temperatures, further extending lamp life and consistency of high-quality light output. Also, because the FastFit design is applied to Philips Halogen lamps, switching between lamp technologies can be done quickly and easily. The Philips MSR Gold™ 1200 FastFit can be operated in a lamp wattage range between 800W and 1400W.

Product data

General Information		Operating and Electrical	
Base	PGJX50 [PGJX50]	Power (Rated) (Nom)	2000 W
Operating Position	Universal [Universal]	Lamp Current (Nom)	15.2 A
Main Application	Entertainment	Ignition Supply Voltage (Min)	198 V
Life to 50% Failures (Nom)	750 h		
System Description	FastFit	Controls and Dimming	
		Dimmable	Yes
Light Technical		Mechanical and Housing	
Color Code	- [Not Specified]	Cap-Base Information	PGJX50
Initial lumen (Min)	162000 lm	Luminaire Design Requirements	
Initial lumen (Nom)	180000 lm	Bulb Temperature (Max)	950 °C
Chromaticity Coordinate X (Nom)	321	Pinch Temperature (Max)	500 °C
Chromaticity Coordinate Y (Nom)	332		
Correlated Color Temperature (Nom)	6050 K	Product Data	
Luminous Efficacy (rated) (Nom)	90 lm/W	Order product name	MSR Gold™ 2000 FastFit 1CT/8
Color Rendering Index (Nom)	91		

MSR Gold™ FastFit

EAN/UPC - Product	8727900919493
Order code	245738
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	8

Material Nr. (12NC)	928176905114
Net Weight (Piece)	0.147 kg

Warnings and Safety

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F
MSR Gold™ 2000 FastFit 1CT/8	34 mm	8.0 mm	66 mm	68 mm	67 mm	134 mm	50 mm

MSR GOLD 2000W FastFit

