



# MASTERCoulour CDM-TC Elite

## MASTERC CDM-TC Elite 70W/942 G8.5 1CT

Single-ended, compact size, high-efficiency Ceramic Metal Halide discharge lamp

### Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Use only with electronic control gear
- Use only with electronic control gear
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


General Information		Luminous Flux	
Cap-Base	G8.5 [G8.5]	Luminous Flux	7,450 lm
Operating Position	UNIVERSAL [Any or Universal (U)]	Color Designation	Cool White (CW)
Flux measurement reference	Sphere	Chromaticity Coordinate X (Nom)	0.371
Life to 50% Failures (Nom)	15,000 hour(s)	Chromaticity Coordinate Y (Nom)	0.366
Light Technical		Correlated Color Temperature (Nom)	4200 K
Color Code	942 [CCT of 4200K]	Luminous Efficacy (rated) (Nom)	102 lm/W
		Color rendering index (CRI)	92

# MASTERC colour CDM-TC Elite

Arc Length O (Nom)	7.75 mm
<b>Operating and Electrical</b>	
Power Consumption	73.2 W
Voltage (Nom)	88 V
Voltage (Nom)	88 V
<b>Controls and Dimming</b>	
Dimmable	No
<b>Mechanical and Housing</b>	
Bulb Finish	Clear
Bulb Shape	T14 [T 14 mm]
<b>Approval and Application</b>	
Energy Efficiency Class	F
Mercury (Hg) Content (Max)	6.6 mg

Mercury (Hg) Content (Nom)	6.6 mg
Energy Consumption kWh/1000 h	74 kWh
EPREL Registration Number	473275
<b>Product Data</b>	
Order product name	MASTERC CDM-TC Elite 70W/942 G8.5 1CT
Full product name	MASTERC CDM-TC Elite 70W/942 G8.5 1CT
Full product code	871829116368800
Order code	928193905131
Material Nr. (12NC)	928193905131
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291163688
Numerator - Packs per outer box	12
EAN/UPC - Case	8718291163695

## Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)
MASTERC CDM-TC Elite 70W/942 G8.5 1CT	15 mm	7.75 mm	51 mm	53 mm	52 mm	85 mm

## Photometric data





Spectral Power Distribution Colour - MASTERC CDM-TC Elite 70W/942 G8.5 1CT

Light Distribution Diagram - MASTERC CDM-TC Elite 70W/942 G8.5 1CT

# MASTERC colour CDM-TC Elite

## Lifetime



Lumen Maintenance Diagram - MASTERC CDM-TC Elite 70W/942 G8.5 1CT

Life Expectancy Diagram - MASTERC CDM-TC Elite 70W/942 G8.5 1CT

