



MASTERColour CDM-Rm 小型精锐型

CDM-Rm Elite Mini 35W/930 GX10 MR16 25D

能够反射更多闪烁光的便捷途径。新的飞利浦 MASTERColour CDM-R 迷你款型将 MASTERColour 可靠的质量带给了 50mm 反射器光源，使其具有超强输出和色彩稳定性，能够营造出适合客户零售品牌和定位的氛围

安全提示

- Use only with electronic control gear
- Control gear must include end-of-life protection (IEC61167, IEC 62035).
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

产品数据

一般信息	
底盖	GX10
操作位置	UNIVERSAL [任意或通用 (U)]
切换循环	1,350
光通量测量参考	Narrow Cone
50% 故障条件下的使用寿命 (标称)	15,000 小时
灯技术	
颜色代码	930 [CCT of 3000K]
光束角度 (标称)	25 °
光通量	2,150 lm
发光强度 (标称)	7,600 cd
色度坐标 X (标称)	0.434
色度坐标 Y (标称)	0.398
相关色温 (标称)	3000 K


光效 (额定)(标称)	60 lm/W
显色指数 (CRI)	90
标称使用寿命结束时灯的光通维持率 (标称)	80 %
90° 圆锥形光通量 (额定)	2,150 lm
操作和电气	
功耗	39.1 W
60% 灯光下的预热时间	120 s
电压 (标称)	87 V
电压 (标称)	87 V
控制和调光	
可调光	否

MASTERCoulour CDM-Rm 小型精锐型

机械和外壳	
灯泡外形	MR16 [2 英寸/50 毫米]
审批和申请	
能效等级	G
汞 (Hg) 含量 (最高)	4.7 mg
汞 (Hg) 含量 (标称)	4.7 mg
能耗 kWh/1000 h	40 kWh
EPREL 注册号	473277


产品数据	
订单产品名称	CDM-Rm Elite Mini 35W/930 GX10 MR16 25D

二维绘图




Product	D (max)	D	C (max)	C	C1 (max)	A (max)
CDM-Rm Elite Mini 35W/930	51 mm	50 mm	65.4 mm	62.75 mm	60.9 mm	59 mm
GX10 MR16 25D						

光度数据



Light Distribution Diagram - CDM-Rm Elite Mini 35W/930 GX10 MR16 25D




Spectral Power Distribution Colour - CDM-Rm Elite Mini 35W/930 GX10 MR16 25D

MASTERColour CDM-Rm 小型精锐型

寿命



Life Expectancy Diagram - CDM-Rm Elite Mini 35W/930 GX10 MR16 25D



Lumen Maintenance Diagram - CDM-Rm Elite Mini 35W/930 GX10 MR16 25D

